
FLOW SWITCH

FMS-FW25



Product description

- For use on liquid lines such as water, ethylene glycol, or any non-corrosive fluid in chillers, pumps, condensers, boilers, etc.
- With S.P.D.T. contact mechanism.
- Paddle consists of three segments that can be removed or trimmed for use in 1 to 6" pipe.

SPECIFICATION ELECTRICAL RATINGS

Rated Voltage(V) Rated Amps(A) Non-Inductive current		Dawn Carr	125V AC	250V AC
		Power Cosp 1		
Locked Rotor current	0.45	21	15	

Pipe Size	Paddle Size	#Adjustment range (L/min)				
		Min.		Max.		
		Flow Decrease	Flow Increase	Flow Decrease	Flow Increase	
1"	1"	18	28	45	55	
1-1/4"		43	53	100	120	
1-1/2"		63	78	135	162	
2"	1"+2"	50	65	150	180	
	1"	151	181	220	264	
2-1/2"	1"+2"	105	126	355	426	
	1"	356	427	360	432	
3"	1"+2"+3"	100	120	225	270	
	1"+2"	226	271	480	576	
	1"	481	577	510	612	
4"	1"+2"+3"	200	240	385	462	
	1"+2"	386	463	820	984	
	1"	821	985	870	1044	